Quiktron

**10FT Red Q-Series Patch Cords CAT6 Booted**

Part No. 576-130-010

Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

## Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Quiktron | Color | Red |
| UPC Number | 884815780162 | Country Of Origin | Vietnam |
| Product Type | Patch Cord | Features | Standard Diameter |
| Application Sector | Commercial, Industrial | Warranty Type | 5-Year |

### Dimensions

| | | | |
|---|---|---|---|
| Product Weight US | 0.25 lb | Product Length US | 10.0 FT |
| Cable Length | 10 ft | | |

### Additional Information

| | |
|---|---|
| RoHS Compliant | Yes |

### Technical Information

| | | | |
|---|---|---|---|
| Operating Temperature Min | -10 °C | Category Performance Application | Cat6 |
| Compatibility | RJ-45 | Wire Gauge | 24 AWG |
| Storage Humidity | 0-90% RH (Non-Condensing) | Plating Specification | 50 µ in Gold |
| Jacket Application | Riser Rated | Bend Radius | 0.896 in |
| Shielded/Unshielded Cable | Unshielded | Termination Style | Pre-Terminated |
| Conductor Stranding | Stranded | Operating Temperature Max | 60 °C |
| Cable Type | Snagless | Jacket Rating | CM Rated |
| Cable Diameter | 0.224 in | Braid | Non-braided Wiring |
| Connector 2 | RJ-45 Male | Connector 1 | RJ-45 Male |
| Operating Temperature | -10°-60°C | Operating Humidity | 0-90% RH (Non-Condensing) |
| Number of Strands | 7 | Conductor Material | Copper |
| Voltage | 300.0 V | Storage Temperature | -40° - 60° C |