Quiktron

1ft Q-Series Cat6a Snagless (UTP) Ethernet Network Patch Cable, CM Rated - Grey

Part No. 576-A00-001

Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

Product Line	Quiktron	Color	Gray
UPC Number	884815793056	Country Of Origin	Vietnam
Product Type	Patch Cord	Features	Standard Diameter
Application Sector	Commercial, Industrial	Warranty Type	5-Year

Dimensions

Product Weight US	0.035 lb	Product Length US	1.0 FT
Cable Length	1 ft		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes

Technical Information

Operating Temperature Min	-10 °C	Category Performance Application	Cat6a
Compatibility	RJ-45	Wire Gauge	26 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Riser Rated	Bend Radius	0.944 in
Shielded/Unshielded Cable	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Stranded	Operating Temperature Max	60 °C
Cable Type	Snagless	Jacket Rating	CM Rated
Cable Diameter	0.236 in	Braid	Non-braided Wiring
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male
Operating Temperature	-10°-60°C	Operating Humidity	0-90% RH (Non-Condensing)
Number of Strands	7	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C