



Quiktron
10ft Q-Series Cat6a Snagless (UTP) Ethernet Network Patch Cable, CM Rated - Green
Part No. 576-A20-010

Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.



Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

Product Line	Quiktron	UPC Number	884815793599
Country Of Origin	Vietnam	Application Sector	Commercial, Industrial
Type	Copper Patch Cord		

Dimensions

Product Weight US	0.35 lb	Product Length US	10.0 FT
-------------------	---------	-------------------	---------

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----