



Quiktron
10ft Q-Series Cat6a Snagless (UTP) Ethernet Network Patch Cable, CM Rated - White
Part No. 576-A25-010

Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.



Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

| | | | |
|---------------|-------------------|--------------------|------------------------|
| Product Line | Quiktron | Color | White |
| UPC Number | 884815793292 | Country Of Origin | Vietnam |
| Features | Standard Diameter | Application Sector | Commercial, Industrial |
| Warranty Type | 5-Year | Type | Copper Patch Cord |

Dimensions

| | | | |
|-------------------|---------|-------------------|---------|
| Product Weight US | 0.35 lb | Product Length US | 10.0 FT |
| Cable Length | 10 ft | | |

Additional Information

| | | | |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|---------------------------|--------|----------------------------------|-------|
| Operating Temperature Min | -10 °C | Category Performance Application | Cat6a |
|---------------------------|--------|----------------------------------|-------|

| | | | |
|---------------|-------|------------|--------|
| Compatibility | RJ-45 | Wire Gauge | 26 AWG |
|---------------|-------|------------|--------|

| | | | |
|------------------|---------------------------|-----------------------|--------------|
| Storage Humidity | 0-90% RH (Non-Condensing) | Plating Specification | 50 μ in Gold |
|------------------|---------------------------|-----------------------|--------------|

| | | | |
|--------------------|-------------|-------------|----------|
| Jacket Application | Riser Rated | Bend Radius | 0.944 in |
|--------------------|-------------|-------------|----------|

| | | | |
|---------------------------|------------|-------------------|----------------|
| Shielded/Unshielded Cable | Unshielded | Termination Style | Pre-Terminated |
|---------------------------|------------|-------------------|----------------|

| | | | |
|---------------------|----------|---------------------------|-------|
| Conductor Stranding | Stranded | Operating Temperature Max | 60 °C |
|---------------------|----------|---------------------------|-------|

| | | | |
|------------|----------|---------------|----------|
| Cable Type | Snagless | Jacket Rating | CM Rated |
|------------|----------|---------------|----------|

| | | | |
|----------------|----------|-------|--------------------|
| Cable Diameter | 0.236 in | Braid | Non-braided Wiring |
|----------------|----------|-------|--------------------|

| | | | |
|-------------|------------|-------------|------------|
| Connector 2 | RJ-45 Male | Connector 1 | RJ-45 Male |
|-------------|------------|-------------|------------|

| | | | |
|-----------------------|-----------|--------------------|---------------------------|
| Operating Temperature | -10°-60°C | Operating Humidity | 0-90% RH (Non-Condensing) |
|-----------------------|-----------|--------------------|---------------------------|

| | | | |
|-------------------|---|--------------------|--------|
| Number of Strands | 7 | Conductor Material | Copper |
|-------------------|---|--------------------|--------|

| | | | |
|---------|---------|---------------------|--------------|
| Voltage | 300.0 V | Storage Temperature | -40° - 60° C |
|---------|---------|---------------------|--------------|
