



Quiktron
Q-Series 28 AWG CAT6 Patch Cable, Orange, 12 FT
Part No. 576-RD40-012



Reduced diameter is ideal for high density data center applications. The smaller cable surface area allows for increased airflow and a smaller bend radius, which makes it easy to route through cable management panels.

Features & Benefits

Reduced Size: 36% reduction in diameter compared to standard Cat6 cables

Standards Compliant: Meets the TIA-568-C.2 standards for patch cord performance

Snagless connector design: Prevents unwanted cable snags during installation and provides extra strain relief

Many Color Options: Available in a variety of colors

Small diameter UTP patch cord: Great for higher-density and limited applications

Specifications

General Info

| | | | |
|-------------------|-------------------|--------------------|------------------------|
| Product Line | Quiktron | UPC Number | 884815787666 |
| Country Of Origin | Vietnam | Application Sector | Commercial, Industrial |
| Type | Copper Patch Cord | | |

Dimensions

| | | | |
|-------------------|----------|-------------------|---------|
| Product Weight US | 0.132 lb | Product Length US | 12.0 FT |
|-------------------|----------|-------------------|---------|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|