



Pass and Seymour
20A 250V Commercial Spec-Grade Single Receptacle, Side Wire, White
Part No. 5850W

Commercial Spec Grade Duplex Receptacle, Side Wire 20A 250V



Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007585018
Country Of Origin	Mexico	Number of Receptacles	1
Application Sector	Commercial	Standard	UL 498, WC596, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor