



Pass and Seymour
20A 250V Heavy Duty Spec-Grade Single Receptacle, Back and Side Wire, White
Part No. 5871W

Heavy-Duty Spec Grade Single Receptacle Back and Side Wire 20A 250V



Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. One-piece heat-treated triple-wipe brass power contacts.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment.
- Auto-ground clip assures positive ground. For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here. Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Type	Outlet		

Dimensions

Product Width US	1.32 in	Product Depth US	1.093 in
Product Height US	1.68 in		

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cULus Listed	Yes
cUL Listed	Yes		

Technical Information

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Voltage	250.0 V		
