



Pass and Seymour
15A, 125V Watertight Duplex Receptacle, Yellow
Part No. 60W47DPLX



Straight Blade Watertight Duplex Receptacle, 15amp 125volt, NEMA Configuration 5-15R, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Lockout/Tagout capability.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033472	Country Of Origin	United States
Application Sector	Commercial	Standard	CSA Listed, FSUL, UL Listed

Technical Information

Phase	Single	Connection	Cable
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG

Environmental Conditions

Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized
