



Pass and Seymour
15A, 250V Watertight Duplex Receptacle, Yellow
Part No. 60W49DPLX



Straight Blade Watertight Duplex Receptacle, 15amp 250volt, NEMA Configuration 6-15, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Commercial
Standard	CSA Listed, FSUL, UL Listed		

Technical Information

Phase	Single	Connection	Cable
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG

Voltage

250.0 V

Environmental Conditions

Moisture Resistance NEMA 3R
(Flip Lid Assemblies/Back
Boxes) Flammability UL94V0
(boxes & wiring device
interiors) UL94V2 (cover
plates) UL94HB (wiring device
housings, flip lid seals)
Operating Temperature -40°C
(without impact) to +60°C
continuous UV Resistance All
exposed materials are UV
stabilized
