



The TracJack, recessed 75 ohm, F-Type, female to female connector, Fog White Adapter Plate, has a single Recessed F-Type, 75Ω, feedthrough connector, mounted at a 180° exit angle. F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras. This adapter panel is 1 unit high. TracJack modules offer flexibility with structured cabling at the workstation or in furniture with a modular design and a wide variety of connectivity options. Intelligent engineering simplifies and speeds up moves, adds, and changes with a front removeable design. Compatible With: All TracJack faceplates

## Features & Benefits

Meets Category 5e standard: Ensures standards compliance.	Low profile connector: Allows furniture to be placed closer to the wall.
Designed for multiple coax cable styles: Accepts both push-style and screw-style.	75 Ohm F-connector: Ideal for cable/satellite TV, cable modems, and security cameras.
Standard TracJack footprint: Fits in all TracJack faceplates and housings.	Front removable module: Less intrusive access for adds, moves, changes.
Integrates with Legrand   Wiremold : Can be used in raceway, floor boxes, Poke-Thru, and work surface portals	

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875834762
Country Of Origin	Taiwan, Province Of China	Application Sector	Commercial/Industrial
Standard	UL Standard	Type	Jack

### Additional Information

RoHS Conformant	Yes
-----------------	-----