



The TracJack, recessed 75 ohm, F-Type, female to female connector, Fog White Adapter Plate, has a single Recessed F-Type, 75?, feedthrough connector, mounted at a 180 Degree exit angle. F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras. This adapter panel is 1 unit high. TracJack modules offer flexibility with structured cabling at the workstation or in furniture with a modular design and a wide variety of connectivity options. Intelligent engineering simplifies and speeds up moves, adds, and changes with a front removable design. Compatible With: All TracJack faceplates

Features & Benefits

Meets Category 5e standard: Ensures standards compliance.

Low profile connector: Allows furniture to be placed closer to the wall.

Designed for multiple coax cable styles: Accepts both push-style and screw-style.

75 Ohm F-connector: Ideal for cable/satellite TV, cable modems, and security cameras.

Standard TracJack footprint: Fits in all TracJack faceplates and housings.

Front removable module: Less intrusive access for adds, moves, changes.

Integrates with Legrand Wiremold : Can be used in raceway, floor boxes, Poke-Thru, and work surface portals.

Specifications

General Info

Product Line	Ortronics	Color	White
UPC Number	662875834779	Country Of Origin	Taiwan, Province Of China
Application Sector	Commercial	Standard	UL Standard
Warranty Type	5-Year	Type	Workstation

Dimensions

Product Width US	0.73 in	Product Depth US	0.875 in
Product Height US	0.92 in		

Technical Information

Connector 2

F-Type Female

Connector 1

F-Type Female

Connectivity Footprint

TracJack
