



Pass and Seymour  
Trademaster® Grounding Toggle Switch, Ivory  
Part No. 664IG

Four-Way Switch, Grounded Terminals, 15 amps, 120 volts, Brown.



## Features & Benefits

Side wire #12 and #14 AWG. Push wire #14 AWG.

Tri-drive ground, terminal, and mounting screws.

Easy-access green hex head ground screw.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498		

### Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		

### Additional Information

---

Product Environmental Profile      Yes

---

### Technical Information

---

Connection	Grounding	Amperage	15 A
Number of Poles	4-Way	Voltage	120.0 V

---