



Pass and Seymour
Trademaster® Grounding Toggle Switch, Ivory
Part No. 664IG

Four-Way Switch, Grounded Terminals, 15 amps, 120 volts, Brown.



Features & Benefits

Side wire #12 and #14 AWG. Push wire #14 AWG.

Tri-drive ground, terminal, and mounting screws.

Easy-access green hex head ground screw.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007664010
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	UL 498		

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection	Grounding	Contact Rating	15 Amp, 120/125 VAC
------------	-----------	----------------	---------------------

Amperage	15 A	Number of Poles	4-Way
----------	------	-----------------	-------

Wire Size	#14 - #10 AWG
-----------	---------------
