



Pass and Seymour
Two Grounding Single-Pole Combination Switches, Brown
Part No. 670G



Single-Pole, Double Combination Switch, 20A, 120/277V, White.

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|-------------------------|------------|--------------|
| Product Line | Pass & Seymour | Color | Brown |
| Finish | Matte | UPC Number | 785007006018 |
| Country Of Origin | Mexico | Features | Combination |
| Application Sector | Commercial, Residential | Standard | UL20 |
| Type | Combination | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.32 in | Product Depth US | 0.94 in |
| Product Height US | 4.06 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------------|-----|------------------|-------|
| Contact Configuration | N-O | Operating Cycles | 30000 |
|-----------------------|-----|------------------|-------|

| | | | |
|------------|-----------|----------------|---------------------|
| Connection | Side Wire | Contact Rating | 20 Amp, 120/277 VAC |
|------------|-----------|----------------|---------------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Single Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|---------------|---------|---------|
| Wire Size | #14 - #10 AWG | Voltage | 120.0 V |
|-----------|---------------|---------|---------|

| | | | |
|--------------------------|-----------------------|--|--|
| Environmental Conditions | Flammability: UL94 V2 | | |
|--------------------------|-----------------------|--|--|