



Pass and Seymour

Discontinued - 20A, 120/125V Combination Single-Pole Switch and Single Receptacle, Brown | Substitute 671TR

Part No. 671

Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.



Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	671TR
Color	Brown	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL20, UL498

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Actuator	Toggle	Connection	Side wire
Contact Rating	20 Amp, 120/125 VAC	Amperage	20 A
Action	SP & Receptacle	Number of Poles	Single Pole
Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2