



Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

Features & Benefits

- Easily accessible break-off separate or common feed. Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Specifications

General Info			
Product Line	Pass & Seymour	Replaced by Part Number	671TRLA
UPC Number	785007671032	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL20, UL498
Type	Combination		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Contact Configuration	N-0	Operating Cycles	30000
Actuator	Toggle	Connection	Side Wire
Contact Rating	20 Amp, 120/125 VAC	Amperage	20 A
Number of Poles	Single Pole	Environmental Conditions	Flammability: UL94 V2