



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Easily accessible break-off separate or common feed.	Side wire #12 and #14 AWG.
Two devices fit into the space of one.	Grounding combination devices meet NEC Requirements.
Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL20, UL498
Type	Combination		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Contact Configuration	N-O
Operating Cycles	30000	Actuator	Toggle
Connection	Side wire	Contact Rating	20 Amp, 120/125 VAC
Amperage	20 A	Action	SP & Recptacle
Number of Poles	Single Pole	Voltage	120.0 V

Environmental Conditions

Flammability: UL94 V2
