



## Pass and Seymour

20A, 3?480V Turnlok® Watertight Single Receptacle, Black  
Part No. 67W76BK



P&S Turnlok watertight receptacles feature impact-resistant Valox lids, cover plates and receptacle bodies that withstand impacts, chemical and corrosion. Ideal for the harsh environments typically found in food & beverage processing plants, petrochemical plants, marinas & shipbuilding locations, mining locations, mills and more.

### Features & Benefits

Impact-resistant Valox lid, cover plate and receptacle body withstand impacts, chemicals and corrosion.

Spring-loaded flip cover provides protection when device is not in use.

Stainless-steel hinge spring and pin ensure corrosion resistance.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### Specifications

#### General Info

Color	Black	UPC Number	785007040715
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL Listed, CSA Listed

#### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

#### Technical Information

Number of Poles	Double Pole	Voltage	125 V
Connection	Screw terminals	Dielectric Strength	Connectors: 2000V AC if rated 300V or less, 3000V AC if rated above 300V. Plugs: 2500V AC if rated 300V or less, 3500V AC if rated above 300V.
Phase	Single	Temperature Rating	-40°C (without impact) to +60°C continuous
Wire Size	#14 - #10 AWG Copper Conductor Only	Number of Wires	3
Environmental Conditions	UL94 HB		