



Pass and Seymour

Discontinued - 15A, 120/277V Decorator Combination Two, Non-Grounding/Single-Pole Switches, Light Almond
Part No. 680LA



Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	RCD11LA
UPC Number	785007191141	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL20
Type	Combination		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Actuator	Toggle	Connection	non-grounding, Side wire

Contact Rating	15Amp, 120/277Vac	Amperage	15 A
Number of Poles	Single Pole	Environmental Conditions	Flammability: UL94 V2