

Single Receptacle 3-Pole 3-Wire 20A 125/250V



## Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

For covering patents, see  
[www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 20		

### Dimensions

Product Width US	1.38 in	Product Depth US	1.15 in
Product Height US	1.75 in		

### Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Single Pole	Wire Size	14 - 12 AWG

---

Voltage

125.0 V

---