



Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------------|-------------|
| Product Line | Pass & Seymour | Replaced by Part Number | 691TRI |
| Color | Ivory | Country Of Origin | Mexico |
| Application Sector | Residential/Commercial | Standard | UL20, UL498 |
| Type | Combination | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------------|---------------------|--------------------------|-----------------------|
| Contact Configuration | N-O | Operating Cycles | 30000 |
| Actuator | Toggle | Connection | Side wire |
| Contact Rating | 15 Amp, 120/125 VAC | Amperage | 15 A |
| Action | SP & Recptacle | Number of Poles | Single Pole |
| Voltage | 120.0 V | Environmental Conditions | Flammability: UL94 V2 |