



Single Pole, Double Switch, 15 amps, 120/277 volts, White.  



## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                        |                         |        |
|--------------------|------------------------|-------------------------|--------|
| Product Line       | Pass & Seymour         | Replaced by Part Number | 690G   |
| Color              | Brown                  | Country Of Origin       | Mexico |
| Application Sector | Residential/Commercial | Standard                | UL20   |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|                       |        |                  |                          |
|-----------------------|--------|------------------|--------------------------|
| Contact Configuration | N-0    | Operating Cycles | 30000                    |
| Actuator              | Toggle | Connection       | Side wire, non-grounding |

---

|                |                     |                          |                       |
|----------------|---------------------|--------------------------|-----------------------|
| Contact Rating | 15 Amp, 120/277 VAC | Amperage                 | 15 A                  |
| Action         | (2) SP              | Number of Poles          | Single Pole           |
| Voltage        | 0.433 V             | Environmental Conditions | Flammability: UL94 V2 |

---