



Pass and Seymour
15A 120V/125V Combination Single-Pole Toggle Switch and Single Receptacle, Light Almond
Part No. 691LA

Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.



Features & Benefits

Easily accessible break-off separate or common feed.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

One-piece heat-treated triple-wipe brass power contacts.

Grounding combination devices meet NEC Requirements.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Indoor
Package Quantity	1	Application Sector	Residential/Commercial
Standard	UL20, UL498	Type	Combination

Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	No	Contact Configuration	N-0
---------------------	----	-----------------------	-----

Operating Cycles	30000	Actuator	Toggle
------------------	-------	----------	--------

Connection	Side wire	Contact Rating	15 Amp, 120/125 VAC
------------	-----------	----------------	---------------------

Amperage	15 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

Is Weather Resistant	No	Indoor/Outdoor	Indoor
----------------------	----	----------------	--------

NEMA Configuration Code	5-15R	Supply Voltage	125 V
-------------------------	-------	----------------	-------

Voltage	120.0 V	Connection Type	Wired
---------	---------	-----------------	-------

Environmental Conditions	Flammability: UL94 V2		
--------------------------	-----------------------	--	--
