



Pass and Seymour
15A 120V/125V Combination Single-Pole Toggle Switch and Single Receptacle, Light Almond
Part No. 691LA



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

Features & Benefits

Easily accessible break-off separate or common feed.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

One-piece heat-treated triple-wipe brass power contacts.

Grounding combination devices meet NEC Requirements.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007691054
Country Of Origin	Mexico	Number of Receptacles	1
Features	Combination	Number of Switches	1
Application Sector	Commercial, Residential	Standard	UL20, UL498
Type	Combination		

Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
------------------	---------	------------------	---------

Product Height US	4.06 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Seismic Tested	No	Is Tamper-Resistant	No
Contact Configuration	N-O	Operating Cycles	30000
Connection	Side Wire	Contact Rating	15 Amp, 120/125 VAC
Amperage	15 A	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Mounting Type	Box
Supply Voltage	125 V	Voltage	120/125 V
Connection Type	Wired	Environmental Conditions	Flammability: UL94 V2