



Pass and Seymour  
15A 120V/125V Combination Single-Pole Toggle Switch and Tamper-Resistant Single Receptacle, Ivory  
Part No. 691TRI



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Easily accessible break-off separate or common feed.

One-piece heat-treated triple-wipe brass power contacts.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects. For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                    |                        |
|-------------------|----------------|--------------------|------------------------|
| Product Line      | Pass & Seymour | Color              | Ivory                  |
| Country Of Origin | Mexico         | Application Sector | Residential/Commercial |
| Standard          | UL20, UL498    | Type               | Combination            |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.32 in | Product Depth US | 1.15 in |
| Product Height US | 4.06 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|                     |       |                       |        |
|---------------------|-------|-----------------------|--------|
| Is Tamper-Resistant | Yes   | Contact Configuration | N-0    |
| Operating Cycles    | 30000 | Actuator              | Toggle |

---

|                          |                       |                |                     |
|--------------------------|-----------------------|----------------|---------------------|
| Connection               | Side wire             | Contact Rating | 15 Amp, 120/125 VAC |
| Amperage                 | 15 A                  | Action         | SP & Receptacle     |
| Number of Poles          | Single Pole           | Voltage        | 120.0 V             |
| Environmental Conditions | Flammability: UL94 V2 |                |                     |

---