



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

## Features & Benefits

- Easily accessible break-off separate or common feed.
- Two devices fit into the space of one.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- One-piece heat-treated triple-wipe brass power contacts.
- Grounding combination devices meet NEC Requirements.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Number of Switches	1
Outlet Type	Indoor	Package Quantity	1
Application Sector	Residential/Commercial	Standard	UL 498
Type	Combination, Outlet, Switch		

### Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	No	Operating Cycles	3000
---------------------	----	------------------	------

Actuator	Toggle	Connection	Side Wire
----------	--------	------------	-----------

Amperage	15 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

Is Weather Resistant	No	Indoor/Outdoor	Indoor
----------------------	----	----------------	--------

NEMA Configuration Code	5-15R	Mounting Type	Box
-------------------------	-------	---------------	-----

Supply Voltage	120 V	Voltage	125.0 V
----------------	-------	---------	---------

Connection Type	Wired	Environmental Conditions	Flammability: UL94 V2
-----------------	-------	--------------------------	-----------------------