



Pass and Seymour  
15A 120V/125V Combination Single-Pole Toggle Switch and Single Receptacle, White  
Part No. 691W



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

## Features & Benefits

Easily accessible break-off separate or common feed.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

One-piece heat-treated triple-wipe brass power contacts.

Grounding combination devices meet NEC Requirements.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007691023
Country Of Origin	Mexico	Number of Receptacles	1
Number of Switches	1	Application Sector	Commercial, Residential
Standard	UL 498	Type	Combination, Outlet, Switch

### Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Seismic Tested	No	Is Tamper-Resistant	No
Operating Cycles	3000	Actuator	Toggle
Connection	Side Wire	Amperage	15 A
Number of Poles	Single Pole	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Mounting Type	Box
Supply Voltage	120 V	Connection Type	Wired
Environmental Conditions	Flammability: UL94 V2		