



Pass and Seymour  
15A 120V/125V Combination Single-Pole Toggle Switch and Single Receptacle, White  
Part No. 691W



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

## Features & Benefits

Easily accessible break-off separate or common feed.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

One-piece heat-treated triple-wipe brass power contacts.

Grounding combination devices meet NEC Requirements.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Number of Switches	1
Outlet Type	Indoor	Package Quantity	1
Application Sector	Residential/Commercial	Standard	UL 498
Type	Combination, Outlet, Switch		

### Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Is Tamper-Resistant	No	Operating Cycles	3000
---------------------	----	------------------	------

---

Actuator	Toggle	Connection	Side Wire
----------	--------	------------	-----------

---

Amperage	15 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

---

Is Weather Resistant	No	Indoor/Outdoor	Indoor
----------------------	----	----------------	--------

---

NEMA Configuration Code	5-15R	Mounting Type	Box
-------------------------	-------	---------------	-----

---

Supply Voltage	120 V	Voltage	125.0 V
----------------	-------	---------	---------

---

Connection Type	Wired	Environmental Conditions	Flammability: UL94 V2
-----------------	-------	--------------------------	-----------------------

---