



Pass and Seymour
Single-Pole Combination Switch and Pilot Light, White
Part No. 692WG

Single-Pole, Single Pilot light, Combination Switch, 15A, 120/125As, White.



Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements. Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL20	Type	Combination

Dimensions

Product Width US	1.32 in	Product Depth US	1.15 in
Product Height US	4.06 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Actuator	Toggle	Connection	Side wire
Contact Rating	120/125 VAC, 15 Amp	Amperage	15 A
Action	SP & Pilot Light	Number of Poles	Single Pole
Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2