



Pass and Seymour  
Single-Pole Combination Switch and Pilot Light, White  
Part No. 692WG

Single-Pole, Single Pilot light, Combination Switch, 15A, 120/125As, White.



## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007006117
Country Of Origin	Mexico	Features	Combination
Application Sector	Commercial, Residential	Standard	UL20
Type	Combination		

### Dimensions

Product Width US	1.32 in	Product Depth US	1.15 in
Product Height US	4.06 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
-----------------------	-----	------------------	-------

Connection	Side Wire	Contact Rating	15 Amp, 120/125 VAC
------------	-----------	----------------	---------------------

Amperage	15 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

Wire Size	#14 - #10 AWG	Voltage	120/125 V
-----------	---------------	---------	-----------

Environmental Conditions	Flammability: UL94 V2		
--------------------------	-----------------------	--	--