

3-way, Single Pilot Light, Combination Switch, 15A, 120/125As, White.



## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements. Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL20	Type	Combination

### Dimensions

Product Width US	1.32 in	Product Depth US	1.15 in
Product Height US	4.06 in		

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Contact Configuration	N-0	Operating Cycles	30000
-----------------------	-----	------------------	-------

---

Actuator	Toggle	Connection	Side wire
----------	--------	------------	-----------

---

Contact Rating	15 Amp, 120/125 VAC	Amperage	15 A
----------------	---------------------	----------	------

---

Action	3W & Pilot Light	Number of Poles	3-Way
--------	------------------	-----------------	-------

---

Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2
---------	---------	--------------------------	-----------------------

---