



3-way, Single Pilot Light, Combination Switch, 15A, 120/125As, White.

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007006193
Country Of Origin	Mexico	Features	Combination
Application Sector	Commercial, Residential	Standard	UL20
Type	Combination		

Dimensions

Product Width US	1.32 in	Product Depth US	1.15 in
Product Height US	4.06 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
-----------------------	-----	------------------	-------

Connection	Side Wire	Contact Rating	15 Amp, 120/125 VAC
------------	-----------	----------------	---------------------

Amperage	15 A	Number of Poles	3-Way
----------	------	-----------------	-------

Wire Size	#14 - #10 AWG	Voltage	120.0 V
-----------	---------------	---------	---------

Environmental Conditions	Flammability: UL94 V2		
--------------------------	-----------------------	--	--