



Single-Pole, 3-way Double Combination Switch, 15A 120/277V, Ivory.

## Features & Benefits

Easily accessible break-off separate or common feed.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007006223
Country Of Origin	Mexico	Features	Combination
Application Sector	Commercial, Residential	Standard	UL20
Type	Combination		

### Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Connection	Side Wire	Contact Rating	15Amp, 120/277Vac
Amperage	15 A	Wire Size	#14 - #10 AWG
Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2