



Eleven outlets. 15' (4.6m) cord. Length 70" (1.8m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Features & Benefits

Eleven outlets with t-slots. 15' (4.6m) cord. Length 70" (1.8m). Computer grade surge protection, 20 Amps.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776118018
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Phase	Single Stage	Frequency Rating	+35dB Hz
Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Mounting Type	Spring Clip
Mounting	Yes	Type of Indicators	Light
Voltage	600.0 V		
