



Wiremold  
**CabinetMate Plug-In Outlet Center Unit / 120V/20A / 70" long / 11 O/L / 15' cord / Computer Grade Surge**  
 Part No. 7011BDS20R



Eleven outlets with t-slots. 15' (4.6m) cord. Length 70" (1.8m). Computer grade surge protection, 20 Amps.

## Features & Benefits

Eleven outlets with t-slots. 15' (4.6m) cord. Length 70" (1.8m). Computer grade surge protection, 20 Amps.

## Specifications

### General Info

Product Line	Wiremold	Color	Black, Gray
UPC Number	786776052701	Country Of Origin	Mexico
Material	Aluminum	Product Series	CabinetMate
Number of Receptacles	11	Features	Surge Protection
Application Sector	Commercial, Residential	Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

### Dimensions

Product Weight US	6.3 lb	Receptacle Spacing	5.75 in
-------------------	--------	--------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Trade Programs

---

USMCA Yes

---

## Additional Information

---

RoHS Compliant Yes

---

## Technical Information

---

Phase	Single Stage	Cord Length	15 ft
Connection	Cord-ended	Class	75
Amperage	20 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Wiring Method	Cord-ended
NEMA Configuration Code	5-20P, 5-20R	Mounting Type	Spring Clip
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V		

---