



Wiremold
CabinetMate Plug-In Outlet Center Unit / 120V/15A/70 long/11 O/L /15' cord
Part No. 7011ULBD



Eleven outlets, 15' (4.6m) cord. Length 70" (1.8m). Receptacle center-to-center 6" (152mm). 15 Amp unit with a 15A resettable circuit breaker.

Features & Benefits

Eleven outlets, 6' (1.8m) cord. Length 70" (1.8m). Receptacle center-to-center 6" (152mm). 15 Amp unit with a 15A resettable circuit breaker.

Specifications

General Info

Product Line	Wiremold	Color	Black, Gray
UPC Number	786776100990	Country Of Origin	Mexico
Material	Aluminum	Product Series	CabinetMate
Receptacle Type	Simplex	Number of Receptacles	11
Features	Resettable Circuit Breaker	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

Dimensions

Product Width US	1.5 in	Product Weight US	5.48 lb
Product Length US	70.0 in	Receptacle Spacing	6 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Single	Cord Length	15 ft
-------	--------	-------------	-------

Amperage	15 A	Enclosure Type	Aluminum
----------	------	----------------	----------

Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
----------------	--------	---------------	------------

NEMA Configuration Code	5-20P, 5-20R	Mounting Type	Spring Clip
-------------------------	--------------	---------------	-------------

Location Rating	Dry	Voltage	125.0 V
-----------------	-----	---------	---------

Environmental Conditions	Dry interior locations		
--------------------------	------------------------	--	--
