



Medium-Duty Dead Front Plug, Black



Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Impact- and corrosion-resistant durable nylon 6 shell material.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

New-design external cord grips provide visible assurance of safe and proper cord retention.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Double dovetail design provides superior protection against cord pull-out forces.

Rounded back contour reduces snags and hang-ups on the job site.

Visible stamped NEMA configuration and device rating.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | United States | Application Sector | Industrial |
| Standard | UL Listed | | |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.531 in | Product Depth US | 2.624 in |
| Product Height US | 1.531 in | | |

Technical Information

| | | | |
|-------|---|-----------------|---|
| Phase | 3 | Number of Wires | 3 |
|-------|---|-----------------|---|

| | | | |
|----------|---------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
| Voltage | 125.0 V | | |