



Pass and Seymour  
Turnlok® Industrial Spec Grade 20A Non-NEMA Flanged Outlet, Gray  
Part No. 7409SS



Nylon Wall Plate Screws, Oval Head Standard Slot, 6 x 32 Thread, Ivory

## Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL Listed

### Dimensions

Product Width US	2.87 in	Product Depth US	1.34 in
Product Height US	2.87 in		

### Technical Information

Phase	3	Number of Wires	4
Amperage	20 A	Number of Poles	3-Way
Voltage	120.0 V		