



Receptacle 4-Wire 20A 120/208Volt Turnlok®

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007893601
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498		

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.37 in		

Technical Information

Phase	Three	Number of Wires	4
-------	-------	-----------------	---

Amperage	20 A	Number of Poles	3-Way
Wire Size	18 - 0 AWG	Voltage	120.0 V