



Receptacle 4-Wire 20A 120/208Volt Turnlok®

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 498

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.37 in		

Technical Information

Phase	3	Number of Wires	4
Amperage	20 A	Number of Poles	3-Way

Wire Size

18 - 0 AWG

Voltage

120.0 V
