

Receptacle Single 15A 125V Turnlok®



Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	United States	Application Sector	Commercial
Standard	UL 498		

Dimensions

Product Width US	1.562 in	Product Depth US	0.922 in
Product Height US	1.75 in		

Technical Information

Number of Wires	2	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG
Voltage	125.0 V		