

Receptacle Single 15A 125V 10A 250V Turnlok®



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	Non-NEMA

Dimensions

Product Width US	1.437 in	Product Depth US	0.97 in
Product Length US	2.3 in		

Technical Information

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

Voltage

125.0 V

Environmental Conditions

Consult the Factory
