



Wiremold
CabinetMate Plug-In Outlet Center Unit / 120V/15A / 77" long / 12 O/L / 6' cord / Computer Grade Surge
 Part No. 7712BCS



Twelve outlets. 6' (1.8m) cord. Length 77" (2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Features & Benefits

Twelve outlets with t-slots. 6' (1.8m) cord. Length 77" (2m). 20A resettable circuit breaker. Computer grade surge protection, 20 Amps.

Specifications

General Info

Product Line	Wiremold	Color	Black, Gray
UPC Number	786776118025	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

Dimensions

Product Width US	77.0 in	Product Weight US	4.96 lb
Product Height US	1.19 in	Product Length US	1.5 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant Yes

Technical Information

Phase Single Stage Cord Length 6 ft

Connection Cord-ended Class 75

Amperage 15 A Short Circuit Rating 36000 Amps [12000 Amps L-N
12000 Amps L-G 12000 Amps N-G]

Response Time <1 ns Wiring Method Cord-ended

Mounting Type Spring Clip Mounting Yes

Type of Indicators Light Voltage 600.0 V
