



Wiremold  
CabinetMate Plug-In Outlet Center Unit / 120V/15A / 77" long / 12 O/L / 6' cord / Computer Grade Surge  
Part No. 7712BCS



Twelve outlets. 6' (1.8m) cord. Length 77" (2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Features & Benefits

Twelve outlets with t-slots. 6' (1.8m) cord. Length 77" (2m). 20A resettable circuit breaker. Computer grade surge protection, 20 Amps.

Specifications

General Info

|                   |                                                   |                    |                        |
|-------------------|---------------------------------------------------|--------------------|------------------------|
| Product Line      | Wiremold                                          | UPC Number         | 786776118025           |
| Country Of Origin | Mexico                                            | Application Sector | Residential/Commercial |
| Standard          | cULus Listed: File E66421 Guide XYBS<br>XUHT VZCA | Type               | PIOC                   |

Dimensions

|                   |         |                   |         |
|-------------------|---------|-------------------|---------|
| Product Width US  | 77.0 in | Product Height US | 1.19 in |
| Product Length US | 1.5 in  |                   |         |

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Buy American Act Compliance

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

|               |              |                      |                                                              |
|---------------|--------------|----------------------|--------------------------------------------------------------|
| Phase         | Single Stage | Frequency Rating     | +35dB Hz                                                     |
| Connection    | Cord-ended   | Class                | 75                                                           |
| Amperage      | 15 A         | Short Circuit Rating | 36000 Amps [12000 Amps L-N<br>12000 Amps L-G 12000 Amps N-G] |
| Response Time | <1 ns        | Mounting Type        | Spring Clip                                                  |
| Mounting      | Yes          | Type of Indicators   | Light                                                        |
| Voltage       | 600 V        |                      |                                                              |