



Wiremold
CabinetMate Plug-In Outlet Center Unit / 120V/20A/77 long/12 O/L /6' cord
Part No. 7712ULBC20R



Twelve 20A outlets with t-slots, 6' (1.8m) cord. Length 77" (2m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker.

Features & Benefits

Twelve 20A outlets with t-slots, 6' (1.8m) cord. Length 77" (2m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776052596
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	12	Application Sector	Commercial
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	1.5 in	Product Length US	77.0 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
-------	--------	------------------	-------

Amperage	20 A	Enclosure Type	Aluminum
----------	------	----------------	----------

Mounting Type	Spring Clip	Voltage	125.0 V
---------------	-------------	---------	---------

Environmental Conditions	Dry interior locations
--------------------------	------------------------
