



Double pole, Single Phase AC Manual Motor Controller 30 amp, 600 watts, Suitable as Motor Disconnect

## Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
--------------	----------------	-------------------	--------

Standard	CSA Listed, UL Listed
----------	-----------------------

### Dimensions

Product Width US	1.825 in	Product Depth US	1.753 in
------------------	----------	------------------	----------

Product Height US	3.67 in
-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

---

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Amperage	30 A
Wattage	600 W	Supply Voltage	120 V
Environmental Conditions	UL94 V2		

---