



Pass and Seymour
Double Pole, Single Phase AC Manual Controller
Part No. 7802MD



Double pole, Single Phase AC Manual Motor Controller 30 amp, 600 volts (max), Suitable as Motor Disconnect

Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007267655
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed

Dimensions

Product Width US	1.825 in	Product Depth US	1.753 in
Product Height US	3.67 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	50000	Connection	Side & Back Wired
Amperage	30 A	Number of Poles	Double Pole
Wire Size	#14 - #10 AWG	Wattage	600 W
Supply Voltage	120 V	Environmental Conditions	UL94 V2