



NEMA 1 Nylon Enclosure with 1/2inch and 3/4inch Knockouts

## Features & Benefits

High horsepower rating of 20HP. Compact design. Gull-wing shaped brass terminal pressure clamps. Constructed of glass-reinforced thermoplastic. Two-point contact arms. One-piece contact carrier.

UL508 and cULus Listing of individual device and assembled device within enclosure. Heavy-duty zinc-plated steel strap. Two brass rivets secure strap to housing.

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals. Oversized silver alloy contacts.

2-3/4 inch hubs (7812-EX and 7813-EX). 2-1/2 inch knockouts on back and 2-1/2 inch -3/4 inch knockouts on top and bottom (7812-P, 7813-P, 7806-P). 2-1/2 inch knockouts on bottom and back (7832 and 7833).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007780659
Country Of Origin	Mexico	Standard	UL Listed
Type	Manual Controller		

### Dimensions

Product Width US	2.825 in	Product Height US	3.91 in
------------------	----------	-------------------	---------

---

Technical Information

Connection	Side & Back Wired	Amperage	30 A
Wire Size	#14 - #10 AWG	Wattage	1 W
Voltage	600.0 V		

---