



Pass and Seymour  
Manual Controller  
Part No. 7813EX



Triple-Pole, Three Phase Switch (7803) in a NEMA 7 and 9 Enclosure for Hazardous Locations. Class I - Groups C, D Class II - Groups E, F, G. 30A, 600Vs. Slotted opening on enclosures allows for lock-out, tag-out functionality.

## Features & Benefits

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007781342
Country Of Origin	United States	Standard	UL Listed
Type	Manual Controller		

### Dimensions

Product Width US	3.375 in	Product Depth US	4.25 in
Product Height US	5.875 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17949
------------	-----	-----------------	-------

### Technical Information

Connection	Side & Back Wired	Amperage	30 A
Wire Size	#14 - #10 AWG	Voltage	600.0 V