



Pass and Seymour Double Pole, Single Phase AC Manual Motor Controller Part No. 7832MD



Double Pole, Single Phase AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.

Features & Benefits

High Horsepower rating of 20HP

Constructed of glass-reinforced thermoplastic

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

For covering patents, see www.legrand.us/patents.

Gull-wing shaped brass terminal pressure clamps

UL508 and cULus Listing of individual device and assembled device within enclosure

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Aluminum
Country Of Origin	United States	Standard	CSA Listed, UL Listed

Dimensions

Product Width US	4.5 in	Product Depth US	1.8 in
Product Height US	5.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Amperage	30 A
Enclosure Type	NEMA 3R	Voltage	600.0 V
Environmental Conditions	UL94 V2		
